

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300281-009
Moore

Moore Collection Two-Light Brushed Nickel White Opal Glass Luxe Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: White Opal Glass Bell Shaped Shade



Length: 12-1/2 in
Depth: 5-1/4 in
Height: 6-3/4 in
H/CTR: 4-3/8 in (glass facing up)

White Opal Glass Bell Shaped Shade

Width: 3-3/8 in
Height: 4-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	(2) G9 Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	6 inches of wire supplied	Lamp Type G9 LED	1-year Limited Warranty
Fixture can be installed with glass facing up or down	120 V	5 W	Fully dimmable with dimmable bulbs.
Canopy covers a standard 4" recessed outlet box: 4.75" W., 0.75" ht., 4.75" depth			