

Project:

Fixture Type:

Location:

Contact:

P300281-012

Moore

Moore Collection Two-Light Satin Brass White Opal Glass Luxe Bath Vanity Light

Category: Bath & Vanity
Finish: Satin Brass (Plated)
Construction: Steel Construction

Glass/Shade: White Opal Glass Bell Shaped Shade



Length: 12-1/2 in Depth: 5-1/4 in Height: 6-3/4 in

H/CTR: 4-3/8 in (glass facing up)

White Opal Glass Bell Shaped Shade

Width: 3-3/8 in Height: 4-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	(2) G9 Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	6 inches of wire supplied	Lamp Type G9 LED	1-year Limited Warranty
	120 V	5 W	
Fixture can be installed with glass			
facing up or down		Fully dimmable with dimmable	
- ,		bulbs.	
Canopy covers a standard 4"			
recessed outlet box: 4.75" W.,			
0.75" ht., 4.75" depth			