

| Project: | | | |
|---------------|--|--|--|
| Fixture Type: | | | |
| Location: | | | |
| Contact: | | | |

P300286-163 Fayette

Inspired from early electric lighting, this bath light will infuse your home with a sense of history. A simple vintage brass bar attached to a backplate supports a curved arm bending to hold a vintage-style light base. A petal-like light shade crafted from clear depression glass for a must-have, artistic touch completes the design.

- A petal-like light shade crafted from clear depression glass for a must-have, artistic touch completes the design.
- A simple vintage brass bar attached to a backplate supports a curved arm bending to hold a vintage-style light base.
- Inspired from early electric lighting, this bath light will infuse your home with a sense of history.
- · Ideal for any bathroom.
- · Perfect for urban industrial, farmhouse, or vintage electric settings.
- Measures 7-1/2-inch width by 7-1/2-inch height.
- Uses one medium base bulb that is sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Vintage Brass (Plated) Construction: Steel Construction

Glass/Shade: Clear glass Cone shaped shade



Width: 7-1/2 in Height: 7-1/2 in Depth: 9-1/2 in H/CTR: 3-1/2 in

Clear glass Cone shaped shade

Width: 7-1/2 in Height: 1-1/8 in

| MOUNTING | ELECTRICAL | LAMPING | ADDITIONAL INFORMATION |
|--|---------------------------|------------------------------|----------------------------|
| Wall mounted | Prewired | Quantity: | CULus Damp Location Listed |
| | | One 60 W max. Medium Base or | |
| Mounting plate for outlet box included | 6 inches of wire supplied | LED equivalent | 1-year Limited Warranty |
| | 120 V | E26 base Porcelain socket | |
| Canopy covers a standard 4" | | | |
| recessed outlet box: 5.125" W., 1" | | | |
| ht., 5.125" depth | | | |