

Project:

Fixture Type:

Location:

Contact:

## P300287-081 Fayette

Inspired from early electric lighting, this bath light will infuse your home with a sense of history. A simple antique nickel bar attached to a backplate supports curved arms bending to hold vintage-style light bases. Petal-like light shades crafted from clear depression glass for a must-have, artistic touch complete the design.

- Petal-like light shades crafted from clear depression glass for a must-have, artistic touch complete the design.
- A simple antique nickel bar attached to a backplate supports curved arms bending to hold vintage-style light bases.
- Inspired from early electric lighting, this bath light will infuse your home with a sense of history.
- · Ideal for any bathroom.
- · Perfect for urban industrial, farmhouse, or vintage electric settings.
- Measures 16-1/2-inch width by 6-1/2-inch height.
- Uses two medium base bulbs that are sold separately (60w max LED or incandescent).
- · Able to be fully dimmable with dimmable bulbs.
- Includes installation instructions and mounting hardware.
- Progress Lighting products are designed for exceptional quality, reliability, and functionality.

Category: Bath & Vanity Finish: Antique Nickel (Plated) Construction: Steel Construction

Glass/Shade: Clear glass Cone shaped shade



Width: 16-1/2 in Height: 6-1/2 in Depth: 9 in H/CTR: 4 in

Clear glass Cone shaped shade

Width: 7-1/2 in Height: 1-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	Prewired	Quantity:	CULus Damp Location Listed
		Two 60 W max. Medium Base or	
Mounting plate for outlet box included	6 inches of wire supplied	LED equivalent	1-year Limited Warranty
	120 V	E26 base Porcelain sockets	
Canopy covers a standard 4"			
recessed outlet box: 5.128" W., 1"			
ht., 5.125" depth			