

Project:

Fixture Type:

Location:

Contact:

P300295-009 Conway

Conway Collection 1-Light Brushed Nickel Clear Seeded Farmhouse Wall Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Seeded Glass Cone



Length: 6 in Extends: 7 in Height: 8-1/4 in

H/CTR: 3-11/16 in (glass facing up)

Clear Seeded Glass Cone Width: 4-3/837 in Height: 5-5/16 in

		Height: 5-5/16 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: one 100 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 5" W., 5" ht., 0.75" depth			