## **PROGRESS** LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:

## P300296-031 Conway

Conway Collection 2-Light Matte Black Clear Seeded Glass Farmhouse Wall Light

Category: Bath & Vanity Finish: Matte Black (Painted) Construction: Steel Construction Glass/Shade: Clear Seeded Glass Cone



Length: 15 in Extends: 7 in Height: 8-1/4 in H/CTR: 3-11/16 in (glass facing up)

Clear Seeded Glass Cone Width: 4-3/837 in Height: 5-5/16 in

		- 10 - 10 -	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 100 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down			

Canopy covers a standard 4" recessed outlet box: 5" W., 5" ht., 0.75" depth