

Project.

Fixture Type: Location:

Contact:

Everlume

Wall or Ceiling Mounted • Damp Location Listed PROGRESS LED

Description:

Everlume Collection 1-Light Brushed Nickel Frosted Glass LED Modern Bath Vanity Linear Panel Light

Specifications:

- Frosted Polystyrene Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Frame covers a standard 4" recessed outlet box: 9.84 in W., 0.78 in ht., 4.37 in depth
- Mounting backplate for outlet box included
- 6 in of wire supplied
- Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,386/81 (LM-79)
ССТ	3000 K
	4000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2019

P300304-009-CS



Dimensions:

Length: 15-15/16 in Extends: 1.38 in Height: 5 in H/CTR: 2-1/2 in

Frosted Polystyrene Diffuser Width: 0.39 in Height: 4 in



Everlume

Wall or Ceiling Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

 $\mathsf{P300304}\text{-}009\text{-}\mathsf{CS}$ is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06	
Eaton SAL06P	
IDevices IDEV009	
Leviton 6672	
Leviton 6674	
Lutron NTEVL-300	
Lutron DVCL-253P	
Lutron Caseta Wireless	
Lutron AYCL-153P	
Lutron SCL-153P	
Lutron TGCL-153-PH-WH	
Lutron MACL-153M	

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.

P300304-009-CS