

Project:
Fixture Type:
Location:

Everlume

Wall or Ceiling Mounted • Damp Location Listed PROGRESS LED

Contact:

Description:

Everlume Collection 1-Light Satin White Frosted Glass LED Modern Bath Vanity Linear Panel Light

Specifications:

- · Frosted Polystyrene Diffuser
- Dimmable to 10% brightness (See Dimming Notes)
- Frame covers a standard 4" recessed outlet box: 9.84 in W., 0.78 in ht., 4.37 in depth
- · Mounting backplate for outlet box included
- 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	17 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,386/81 (LM-79)
CCT	3000 K
	4000 K
CRI	90 CRI
Life (hours)	60000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cCSAus Damp Location Listed
	Meets California Title 24 JA8-2019

P300304-028-CS



Dimensions:

Length: 15-15/16 in Extends: 1.38 in Height: 5 in H/CTR: 2-1/2 in

Frosted Polystyrene Diffuser

Width: 0.39 in Height: 4 in



Everlume

Wall or Ceiling Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P300304-028-CS

 ${\rm P300304\text{-}028\text{-}CS}$ is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Eaton AAL06

Eaton SAL06P

IDevices IDEV009

Leviton 6672

Leviton 6674

Lutron NTEVL-300

Lutron DVCL-253P

Lutron Caseta Wireless

Lutron AYCL-153P

Lutron SCL-153P

Lutron TGCL-153-PH-WH

Lutron MACL-153M

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.