

Project:

Fixture Type:

Location:

P300312-031-30

Contact:

Pearl LED

Wall Mounted • Damp Location Listed PROGRESS LED

Description:

Pearl LED Collection 3-Light Matte Black Opal Glass LED Modern Bath Vanity Light

Specifications:

- · Opal Glass Globe
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 18 in W., 5 in ht., 1.25 in depth
- · Mounting backplate for outlet box included
- 6 in of wire supplied

Performance:

| Number of Modules | 3 |
|------------------------|------------------------------------|
| Input Power | 19.5 W |
| Input Voltage | 120 V |
| Input Frequency | 60 Hz |
| Lumens/LPW (Delivered) | 1,292/66 (LM-79) |
| ССТ | 3000 K |
| CRI | 90 CRI |
| Life (hours) | 50000 (L70/TM-21) |
| EMI/RFI | FCC Title 47, Part 15, Class B |
| Warranty | 5-year Limited Warranty |
| Labels | cETLus Damp Location Listed |
| | Meets California Title 24 JA8-2019 |
| | |



Dimensions:

Length: 18 in Extends: 5-1/2 in Height: 5 in

H/CTR: 2-1/2 (glass facing up)

Opal Glass Globe Width: 4 in Height: 4 in



Pearl LED

Wall Mounted • Damp Location Listed PROGRESS LED

Dimming Notes:

P300312-031-30

P300312-031-30 is designed to be compatible with many ELV controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls:

Lutron_DVELV-300P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.