

Project:

Fixture Type:

Location:

Contact:

P300315-015 Ashford

Ashford Collection 2-Light Polished Chrome Opal Glass Farmhouse Wall Light

Category: Bath & Vanity Finish: Polished Chrome (Plated) Construction: Steel Construction Glass/Shade: Opal Glass Cone



Length: 14-1/2 in Extends: 8 in Height: 10 in

H/CTR: 5-1/16 in (glass facing up)

Opal Glass Cone Width: 5-5/16 in Height: 5-1/4 in

		Height: 5-1/4 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 100 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 5" W., 5" ht., 1" depth			