

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300317-009
Ashford

Ashford Collection 4-Light Brushed Nickel Opal Glass Farmhouse Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Opal Glass Cone

Length: 33-1/2 in
Extends: 8 in
Height: 10 in
H/CTR: 5-1/16 in (glass facing up)

Opal Glass Cone
Width: 5-5/16 in
Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: four 100 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty

Fixture can be installed with glass facing up or down

Canopy covers a standard 4" recessed outlet box: 5" W., 5" ht., 1" depth