

Project:

Fixture Type:

Location:

Contact:

P300321-009 Aiken

Aiken Collection 2-Light Brushed Nickel Clear Glass Vintage Wall Light

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylinder



Length: 14-5/8 in Extends: 7 in Height: 9-7/8 in

H/CTR: 4-3/16 in (glass facing up)

Clear Glass Cylinder Width: 4-3/16 in

		Height: 5-7/8 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 60 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down			
Canopy covers a standard 4" recessed outlet box: 7.125" W., 4.5" ht., 0.75" depth			