

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



**P300323-009**  
**Aiken**

Aiken Collection 4-Light Brushed Nickel Clear Glass Vintage Bath Vanity Light

**Category:** Bath & Vanity  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Cylinder

Length: 32-1/4 in  
Extends: 7 in  
Height: 9-7/8 in  
H/CTR: 4-3/16 in (glass facing up)

Clear Glass Cylinder  
Width: 4-3/16 in  
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: four 60 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty

Fixture can be installed with glass facing up or down

Canopy covers a standard 4" recessed outlet box: 7.125" W., 4.5" ht., 0.75" depth