

Project:

Fixture Type:

Location:

Contact:

P300328-009 Merry

Merry Collection 2-Light Brushed Nickel Etched Glass Transitional Wall Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical



Length: 12 in Extends: 5-3/4 in Height: 8-1/4 in H/CTR: 6 in

Etched Glass Cylindrical

Width: 4 in Height: 5-3/8 in

	Height: 5-3/8 in		
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 100 W max.	cULus Damp Location Listed
Mounting plate for outlet box included	120 V	E26 base Porcelain Socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 12" W., 4.37" ht., 0.75" depth			