



Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300329-015 Merry

Merry Collection Three-Light Polished Chrome and Etched Glass Transitional Style Bath Vanity Wall Light

Category: Bath & Vanity
Finish: Polished Chrome (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical

Width: 24 in
Extends: 5-3/4 in
Height: 8-1/4 in
H/CTR: 6 in (glass facing up)

Etched Glass Cylindrical
Width: 4 in
Height: 5-3/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 23.75" W., 4" ht., 0.75" depth		Fully dimmable with dimmable bulbs	