

Project:
Fixture Type:

Location:
Contact:

Grid LED

Wall Mounted • Damp Location Listed PROGRESS LED



### **Description:**

Grid LED Collection 1-Light Black White Linen Glass LED Modern Wall Light

### **Specifications:**

- · White Linen Acrylic Shade
- · Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 8.25 in W., 4.75 in ht., 1.125 in depth
- · Mounting backplate for outlet box included
- 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

#### **Performance:**

Number of Modules	1
Input Power	14 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	569/45 (LM-79)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2019

# P300331-031-30



#### **Dimensions:**

Length: 14 in Extends: 3-1/8 in Height: 4-3/4 in

H/CTR: 2-3/8 in (glass facing up)

White Linen Acrylic Shade

Width: 1-11/16 in Height: 3-11/16 in



## **Grid LED**

Wall Mounted • Damp Location Listed PROGRESS LED



#### **Dimming Notes:**

 ${\tt P300331\text{-}031\text{-}30}\ is\ designed\ to\ be\ compatible\ with\ many\ Triac/Forward\ Phase\ ELV/Reverse\ Phase\ controls.$ 

The following is a partial list of known compatible dimmer controls.

# P300331-031-30

#### **Dimming Controls:**

Leviton 6674

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron TGCL-153-PH-WH

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation.

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.