

Project:
Fixture Type:

Location:
Contact:

Grid LED

Wall Mounted · Damp Location Listed PROGRESS LED



Description:

Grid LED Collection 1-Light Silver Ridge White Linen Glass LED Modern Wall Light

Specifications:

- · White Linen Acrylic Shade
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" recessed outlet box: 8.25 in W., 4.75 in ht., 1.125 in depth
- · Mounting backplate for outlet box included
- 6 in of wire supplied
- · Americans With Disabilities Act (ADA) compliant

Performance:

Number of Modules	1
Input Power	34 W
Input Voltage	120 VAC
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1,639/46 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50000 (L70/TM-21)
EMI/RFI	FCC Title 47, Part 15, Class B
Warranty	5-year Limited Warranty
Labels	cETLus Damp Location Listed
	ENERGY STAR® qualified
	Meets California Title 24 JA8-2019





Dimensions:

Length: 30 in Extends: 3-1/8 in Height: 4-3/4 in

H/CTR: 2-3/8 in (glass facing up)

White Linen Acrylic Shade

Width: 1-11/16 in Height: 3-11/16 in



Grid LED

Wall Mounted • Damp Location Listed PROGRESS LED



Dimming Notes:

P300333-134-30 is designed to be compatible with many Triac/Forward Phase ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

P300333-134-30

Dimming Controls:

IDevices IDEV009

Lutron NTEVL-300

Lutron DVELV-300P

Lutron DVCL-253P

Lutron Caseta Wireless

Lutron AYCL-153P

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation

Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.