

Project:

Fixture Type:

Location:

Contact:

P300342-009

League

League Collection Two-Light Brushed Nickel and Etched Glass Modern Farmhouse Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical



Length: 13-5/8 in Extends: 5-1/2 in Height: 7-5/8 in

H/CTR: 5 in (glass facing up)

Etched Glass Cylindrical

Width: 4-1/8 in Height: 5-1/2 in

		Height: 5-1/2 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: two 100 W max. A19 or LED	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	equivalent	1-year Limited Warranty
		E26 base Porcelain Socket	
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable	
racing up or down		bulbs	
Canopy covers a standard 4"			
recessed outlet box: 7" W., 4.5" ht., 0.75" depth			