

Project:		
Fixture Type:		
Location:		
Contact:		



P300343-009

League

League Collection Three-Light Brushed Nickel and Etched Glass Modern Farmhouse Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Etched Glass Cylindrical

Length: 23 in Extends: 5-1/2 in Height: 7-5/8 in

H/CTR: 5 in (glass facing up)

Etched Glass Cylindrical Width: 4-1/8 in

		Height: 5-1/2 in	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: three 100 W max. A19 or LED	cULus Damp Location Listed
Mounting plate for outlet b included	oox 120 VAC	equivalent	1-year Limited Warranty
		E26 base Porcelain Socket	
Fixture can be installed with	glass		
facing up or down		Fully dimmable with dimmable bulbs	
Canopy covers a standard recessed outlet box: 7" W., 4 ht., 0.75" depth			