## **PROGRESS** LIGHTING<sup>™</sup>

Project:	
ixture Type:	
ocation:	

Contact:



## P300344-009 League

League Collection Four-Light Brushed Nickel and Etched Glass Modern Farmhouse Bath Vanity Light

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Etched Glass Cylindrical

ht., 0.75" depth

Length: 32-1/2 in Extends: 5-1/2 in Height: 7-5/8 in H/CTR: 5 in (glass facing up)

Etched Glass Cylindrical Width: 4-1/8 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	Quantity: four 100 W max. A19 or LED	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	equivalent	1-year Limited Warranty
		E26 base Porcelain Socket	
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5"			