

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300347-009 Caisson

Caisson Collection Three-Light Brushed Nickel Clear Glass Urban Industrial Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell

Length: 23-1/4 in
Extends: 7-1/2 in
Height: 8-7/8 in
H/CTR: 6-5/8 (glass facing up)

Clear Glass Bell
Width: 6 in
Height: 5-7/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	CULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	