

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300349-009 Hinton

Hinton Collection Two-Light Brushed Nickel Clear Seeded Glass Farmhouse
Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Seeded Glass Cone



Length: 15-1/2 in
Extends: 7-1/8 in
Height: 7-3/4 in
H/CTR: 5-1/8 in (glass facing up)

Clear Seeded Glass Cone
Width: 6-1/2 in
Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	CULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 8" W., 5" ht., 1" depth		Fully dimmable with dimmable bulbs	