## PROGRESS LIGHTING<sup>™</sup>

Project:

Fixture Type:

Location:

Contact:



## P300350-009 Hinton

Hinton Collection Three-Light Brushed Nickel Clear Seeded Glass Farmhouse Bath Vanity Light

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Seeded Glass Cone

Length: 24-1/2 in Extends: 7-1/8 in Height: 7-3/4 in H/CTR: 5-1/8 in (glass facing up)

Clear Seeded Glass Cone Width: 6-1/2 in Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	CULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 8" W., 5" ht., 1" depth		Fully dimmable with dimmable bulbs	