

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



**P300350-163**  
**Hinton**

Hinton Collection Three-Light Vintage Brass Clear Seeded Glass Farmhouse Bath Vanity Light

**Category:** Bath & Vanity  
**Finish:** Vintage Brass (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Seeded Glass Cone

Length: 24-1/2 in  
Extends: 7-1/8 in  
Height: 7-3/4 in  
H/CTR: 5-1/8 in (glass facing up)

Clear Seeded Glass Cone  
Width: 6-1/2 in  
Height: 5 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	CULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 8" W., 5" ht., 1" depth		Fully dimmable with dimmable bulbs	