

Project:			
Fixture Type:			
Location:			
Contact:			

P300356-163

Elara

Elara Collection One-Light New Traditional Vintage Brass Clear Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Width: 4-3/4 in Extends: 5 in Height: 11-1/2 in H/CTR: 6 in

Clear Glass Cylindrical

Width: 3 in Height: 8-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Construction of the dead All		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		000.101	
recessed outlet box: 4.75" W., 7.5" ht., 1" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	