



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300356-31M

Elara

Elara Collection One-Light New Traditional Matte Black Clear Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical



Width: 4-3/4 in
 Extends: 5 in
 Height: 11-1/2 in
 H/CTR: 6 in

Clear Glass Cylindrical
 Width: 3 in
 Height: 8-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.5" ht., 1" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	