PROGRESS LIGHTING

roject:	
ixture Type:	
ocation:	

Contact:

P300357-163 Elara

Elara Collection Two-Light New Traditional Vintage Brass Clear Glass Bath Vanity Light

Category: Bath & Vanity Finish: Vintage Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical



Width: 12-1/2 in Extends: 5-1/8 in Height: 11-1/2 in H/CTR: 6-3/4 in

Clear Glass Cylindrical Width: 3 in Height: 8-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Canopy covers a standard 4"		socket	
recessed outlet box: 7.5" W., 4.75" ht., 1" depth		LED: 12.5-watt MAX per socket	
		Fully dimmable with dimmable bulbs	