



Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300357-31M

Elara

Elara Collection Two-Light New Traditional Matte Black Clear Glass Bath Vanity Light

- Category:** Bath & Vanity
- Finish:** Matte Black (Painted)
- Construction:** Steel Construction
- Glass/Shade:** Clear Glass Cylindrical



Width: 12-1/2 in
 Extends: 5-1/8 in
 Height: 11-1/2 in
 H/CTR: 6-3/4 in

Clear Glass Cylindrical
 Width: 3 in
 Height: 8-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 7.5" W., 4.75" ht., 1" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	