

Project:			
Fixture Type:			
Location:			
Contact:			

P300358-163

Elara

Elara Collection Three-Light Vintage Brass Clear Glass New Traditional Bath Vanity Light

Category: Bath & Vanity
Finish: Vintage Brass (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylinder



Length: 22-1/8 in Extends: 5-1/8 in Height: 11-1/2 in H/CTR: 6-3/4 in

Clear Glass Cylinder Length: 3 in Width: 3 in Height: 7-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(3) Candelabra Base (E12) Lamp Type	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 7.5" W., 4.75" ht., 1" depth		Fully dimmable with dimmable bulbs.	