

Project:		
Fixture Type:		
Location:		
Contact:		



P300359-009

Elara

Elara Collection Four-Light New Traditional Brushed Nickel Clear Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Cylindrical

Width: 31-5/8 in Extends: 5-1/8 in Height: 11-1/2 in H/CTR: 6-3/4 in

Clear Glass Cylindrical

Width: 3 in Height: 8-3/4 in

MOUNTING		ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 i	nches of wire supplied	(4) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for out included	let box	120 VAC	Lamp Type B10	1-year Limited Warranty
			Incandescent: 60-watt MAX per	
Canopy covers a stand	dard 4"		socket	
recessed outlet box: 7.5" ht., 1" depth	W., 4.75"		LED: 12.5-watt MAX per socket	
, ,			Fully dimmable with dimmable bulbs	