

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



## P300359-163

### Elara

Elara Collection Four-Light New Traditional Vintage Brass Clear Glass Bath Vanity Light

**Category:** Bath & Vanity  
**Finish:** Vintage Brass (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Cylindrical

Width: 31-5/8 in  
 Extends: 5-1/8 in  
 Height: 11-1/2 in  
 H/CTR: 6-3/4 in

Clear Glass Cylindrical  
 Width: 3 in  
 Height: 8-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Candelabra Base (E12) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type B10	1-year Limited Warranty
Canopy covers a standard 4" recessed outlet box: 7.5" W., 4.75" ht., 1" depth		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket Fully dimmable with dimmable bulbs	