

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_

**P300361-009**  
**Calais**

Calais Collection Two-Light New Traditional Brushed Nickel Clear Glass Bath Vanity Light

**Category:** Bath & Vanity  
**Finish:** Brushed Nickel (Plated)  
**Construction:** Steel Construction  
**Glass/Shade:** Clear Glass Cone



Width: 14-5/8 in  
Extends: 6-1/2 in  
Height: 8-1/2 in  
H/CTR: 5-1/2 in (glass facing up)

Clear Glass Cone  
Width: 5 in  
Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 0.75" ht., 4.5" depth		Fully dimmable with dimmable bulbs	