PROGRESS LIGHTING

Project:			
Fixture Type:			
Location:			

Contact:



Calais Collection Three-Light Brushed Nickel Clear Glass New Traditional Bath Vanity Light

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cone Shaped Bowl



Length: 24-1/4 in Extends: 6-1/2 in Height: 8-1/2 in H/CTR: 5-1/2 in (glass facing up)

Clear Glass Cone Shaped Bowl Length: 5 in Width: 5 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall horizontal	6 inches of wire supplied	(3) Medium Base (E26) Lamp Type	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Fully dimmable with dimmable bulbs.	
Canopy covers a standard 4" recessed outlet box: 7" W., 0.75" ht., 4.5" depth			