

Project:			
Fixture Type:			
Location:			
Contact:			



P300363-31M Calais

Calais Collection Four-Light New Traditional Matte Black Clear Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction
Glass/Shade: Clear Glass Cone

Width: 34 in Extends: 6-1/2 in Height: 8-1/2 in

H/CTR: 5-1/2 in (glass facing up)

Clear Glass Cone Width: 5 in Height: 6 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass		Incandescent: 60-watt MAX per socket	
facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7" W., 0.75" ht., 4.5" depth		Fully dimmable with dimmable bulbs	