PROGRESS LIGHTING^{**}

Project:			
Fixture Type:			
Location:			

Contact:

P300368-009 Cowan

Cowan Collection One-Light Modern Brushed Nickel Etched Opal Glass Bath Vanity Light

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Etched Opal Glass Cylindrical



Width: 4-3/4 in Extends: 5-1/2 in Height: 8-1/2 in H/CTR: 4-9/16 in (glass facing up)

Etched Opal Glass Cylindrical Width: 3-1/2 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION	
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed	
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty	
Fixture can be installed with glass facing up or down	Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket			
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.81" ht., 0.81" depth				