

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P300368-012
Cowan

Cowan Collection One-Light Modern Satin Brass Etched Opal Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Satin Brass (Plated)
Construction: Steel Construction
Glass/Shade: Etched Opal Glass Cylindrical



Width: 4-3/4 in
Extends: 5-1/2 in
Height: 8-1/2 in
H/CTR: 4-9/16 in (glass facing up)

Etched Opal Glass Cylindrical
Width: 3-1/2 in
Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.81" ht., 0.81" depth		Fully dimmable with dimmable bulbs	