

Project:			
Fixture Type:			
Location:			
Contact			

P300368-31M

Cowan

Cowan Collection One-Light Modern Matte Black Etched Opal Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction

Glass/Shade: Etched Opal Glass Cylindrical



Width: 4-3/4 in Extends: 5-1/2 in Height: 8-1/2 in

H/CTR: 4-9/16 in (glass facing up)

Etched Opal Glass Cylindrical

Width: 3-1/2 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION		
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed		
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty		
		Incandescent: 100-watt MAX per			
Fixture can be installed with glass		socket			
facing up or down		LED: 17.5-watt MAX per socket			
Canopy covers a standard 4" recessed outlet box: 4.75" W., 7.81" ht., 0.81" depth					