

Project:			
Fixture Type:			
Location:			
Contact:			

## P300369-009

## Cowan

Cowan Collection Two-Light Modern Brushed Nickel Etched Opal Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Etched Opal Glass Cylindrical



Width: 13-1/2 in Extends: 5-1/2 in Height: 8-1/2 in

H/CTR: 6-1/8 in (glass facing up)

Etched Opal Glass Cylindrical

Width: 3-1/2 in Height: 5-1/2 in

MOUNTING		ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted		6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate fo box included	r outlet	120 VAC	Lamp Type A19	1-year Limited Warranty
			Incandescent: 100-watt MAX per	
Fixture can be installed v	with glass		socket	
facing up or dow	•		LED: 17.5-watt MAX per socket	
Canopy covers a stand recessed outlet box: 7 4.75" ht., 0.81" dep	.81" W.,	Fully dimmable with dimmable bulbs		