

Project:		
Fixture Type:		
Location:		
Contact:		



## P300370-31M

## Cowan

Cowan Collection Three-Light Modern Matte Black Etched Opal Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction

Glass/Shade: Etched Opal Glass Cylindrical

Width: 23-1/2 in Extends: 7-3/4 in Height: 8-1/2 in

H/CTR: 6-1/8 in (glass facing up)

Etched Opal Glass Cylindrical

Width: 3-1/2 in Height: 5-1/2 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting backplate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4"	Fully dimmable with dimmable		
recessed outlet box: 7.81" W., 4.75" ht., 0.81" depth		bulbs	