PROGRESS LIGHTING

Project:		
Fixture Type:		

Location:

Contact:



P300372-012 Adley

Adley Collection Six-Light New Traditional Satin Brass Clear Glass Bath Vanity Light

Category: Bath & Vanity Finish: Satin Brass (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Cylindrical

Width: 48-1/2 in Extends: 6 in Height: 7-5/8 in H/CTR: 5-3/8 in (glass facing up)

Clear Glass Cylindrical Width: 3-3/8 in Height: 5-3/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(6) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 7.75" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	