

Project:		
Fixture Type:		
Location:		
Contact:		

P300373-015

Ambrose

Ambrose Collection One-Light Farmhouse Polished Chrome Clear Glass Bath Vanity Light

Category: Bath & Vanity

Finish: Polished Chrome (F

Finish: Polished Chrome (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Bell



Width: 5 in Extends: 6-1/2 in Height: 7-7/8 in

H/CTR: 5-1/2 in (glass facing up)

Clear Glass Bell Width: 5 in Height: 4-9/16 in

	MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
	Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
1,	/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
			Incandescent: 60-watt MAX per	
Fi	xture can be installed with glass		socket	
	facing up or down		LED: 12.5-watt MAX per socket	
	Canopy covers a standard 4"		Fully dimmable with dimmable	
r	ecessed outlet box: 4.75" W., 1" ht., 4.75" depth		bulbs	