

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300375-015
Ambrose

Ambrose Collection Three-Light Farmhouse Polished Chrome Clear Glass
Bath Vanity Light

Category: Bath & Vanity
Finish: Polished Chrome (Plated)
Construction: Steel Construction
Glass/Shade: Clear Glass Bell

Width: 21 in
Extends: 6-1/2 in
Height: 7-7/8 in
H/CTR: 5-1/2 in (glass facing up)

Clear Glass Bell
Width: 5 in
Height: 4-9/16 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
1/8 IP mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 4.75" W., 1" ht., 4.75" depth		Fully dimmable with dimmable bulbs	