

Project:

Fixture Type:

Location:

Contact:

P300378-009 Gilmour

Gilmour Collection Two-Light Modern Farmhouse Brushed Nickel Clear Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Brushed Nickel (Plated)
Construction: Steel Construction

Glass/Shade: Clear Glass Square/Rectangular



Width: 12-1/4 in Extends: 5-1/2 in Height: 7 in

H/CTR: 4-7/8 in (glass facing up)

Clear Glass Square/Rectangular

Width: 4-3/8 in Height: 5-1/8 in

		0 , 1	
MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(2) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 60-watt MAX per	
Fixture can be installed with glass		socket	
facing up or down		LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 6.75" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	