

Project:

Fixture Type:

Location:

Contact:



P300379-31M Gilmour

Gilmour Collection Three-Light Modern Farmhouse Matte Black Clear Glass Bath Vanity Light

Category: Bath & Vanity
Finish: Matte Black (Painted)
Construction: Steel Construction

Glass/Shade: Clear Glass Square/Rectangular

Width: 20-1/8 in Extends: 5-1/2 in Height: 7 in

H/CTR: 4-7/8 in (glass facing up)

Clear Glass Square/Rectangular

Width: 4-3/8 in Height: 5-1/8 in

			g - ,	
	MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
	Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Swi	vel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
			Incandescent: 60-watt MAX per	
Fixtu	ire can be installed with glass		socket	
	facing up or down		LED: 12.5-watt MAX per socket	
	anopy covers a standard 4" ssed outlet box: 6.75" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	