PROGRESS LIGHTING[™]

Project:		
Fixture Type:		
Location:		

Contact:



P300380-009 Gilmour

Gilmour Collection Four-Light Modern Farmhouse Brushed Nickel Clear Glass Bath Vanity Light

Category: Bath & Vanity Finish: Brushed Nickel (Plated) Construction: Steel Construction Glass/Shade: Clear Glass Square/Rectangular

Width: 27-7/8 in Extends: 5-1/2 in Height: 7 in H/CTR: 4-7/8 in (glass facing up)

Clear Glass Square/Rectangular Width: 4-3/8 in Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 12.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 6.75" W., 4.5" ht., 0.75" depth		Fully dimmable with dimmable bulbs	