

Project:		
Fixture Type:		
Location:		
Contact:		

## P300381-015 Dalton

 ${\bf Dalton\ Collection\ One-Light\ Farmhouse\ Polished\ Chrome\ Metal\ Shade\ Bath\ Vanity\ Light}$ 

Category: Bath & Vanity

Finish: Polished Chrome (Plated) with Coastal Blue accent

**Construction:** Steel Construction **Glass/Shade:** Coastal Blue Metal Dome



Width: 5-1/2 in Extends: 7-3/8 in Height: 9 in

H/CTR: 4-1/4 in (shade facing up)

Coastal Blue Metal Dome Width: 5-1/2

in

Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(1) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with		socket	
shade facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable	
recessed outlet box: 5" W., 0.875" ht., 5" depth		bulbs	