

Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact: \_\_\_\_\_



**P300383-163**  
**Dalton**

Dalton Collection Three-Light Farmhouse Vintage Brass Metal Shade Bath Vanity Light

**Category:** Bath & Vanity  
**Finish:** Vintage Brass (Plated) with Matte Black accent  
**Construction:** Steel Construction  
**Glass/Shade:** Matte Black Metal Dome

Width: 24 in  
Extends: 7-3/8 in  
Height: 9 in  
H/CTR: 4-1/4 in (shade facing up)

Matte Black Metal Dome  
Width: 5-1/2 in  
Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(3) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with shade facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.875" ht., 5" depth		Fully dimmable with dimmable bulbs	