

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300384-015

Dalton

Dalton Collection Four-Light Farmhouse Polished Chrome Metal Shade Bath Vanity Light

Category: Bath & Vanity

Finish: Polished Chrome (Plated) with Coastal Blue accent

Construction: Steel Construction

Glass/Shade: Coastal Blue Metal Dome

Width: 33 in
 Extends: 7-3/8 in
 Height: 9 in
 H/CTR: 4-1/4 in (shade facing up)

Coastal Blue Metal Dome Width:
 5-1/2 in
 Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with shade facing up or down		Incandescent: 100-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 5" W., 0.875" ht., 5" depth		Fully dimmable with dimmable bulbs	