

Project:	
Fixture Type:	
Location:	
Contact:	



P300384-163

Dalton

Dalton Collection Four-Light Farmhouse Vintage Brass Metal Shade Bath Vanity Light

Category: Bath & Vanity

Finish: Vintage Brass (Plated) with Matte Black accent

Construction: Steel Construction **Glass/Shade:** Matte Black Metal Dome

Width: 33 in Extends: 7-3/8 in Height: 9 in

H/CTR: 4-1/4 in (shade facing up)

Matte Black Metal Dome

Width: 5-1/2 in Height: 5-1/4 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(4) Medium Base (E26) Socket	cULus Damp Location Listed
Mounting plate for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
		Incandescent: 100-watt MAX per	
Fixture can be installed with		socket	
shade facing up or down		LED: 17.5-watt MAX per socket	
Canopy covers a standard 4"		Fully dimmable with dimmable	
recessed outlet box: 5" W., 0.875" ht., 5" depth		bulbs	