

Project: _____

Fixture Type: _____

Location: _____

Contact: _____



P300385-009 Replay

Replay Collection Six-Light Traditional Brushed Nickel Etched White Glass
Bath Vanity Light

Category: Bath & Vanity

Finish: Brushed Nickel (Plated)

Construction: Steel Construction

Glass/Shade: Etched White Glass Cylindrical

Width: 48 in
Extends: 6 in
Height: 7-5/8 in
H/CTR: 5-3/8 in (glass facing up)

Etched White Glass Cylindrical
Width: 3-7/8 in
Height: 5-1/8 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Wall mounted	6 inches of wire supplied	(6) Medium Base (E26) Socket	cULus Damp Location Listed
Swivel mounting strap for outlet box included	120 VAC	Lamp Type A19	1-year Limited Warranty
Fixture can be installed with glass facing up or down		Incandescent: 60-watt MAX per socket LED: 17.5-watt MAX per socket	
Canopy covers a standard 4" recessed outlet box: 8.25" W., 4.5" ht., 0.87" depth		Fully dimmable with dimmable bulbs	